

**Rowmark.**  
europe

Schaarbeekstraat 44  
9120 Beveren - Waas  
Belgium  
P +32 3 870 41 10  
F +32 3 877 83 15  
VAT: BE 0807909040

 **FERRO**  
Where innovation  
delivers performance™

**CerMark®**

**ULTRA**  
UNLIMITED POSSIBILITIES



**Ferro and the CerMark Research & Development team is pleased to announce the release of their new product CerMark **ULTRA**.**

This new product is specifically formulated to laser mark on all laser markable substrates such as metals, glass, ceramics and more using just one CerMark product.

CerMark **ULTRA** renews the tradition set by our LMM-6000 as the industry leader. With the introduction of the NEW patent pending CerMark **ULTRA** the standard of excellence continues.

**ULTRA** was formulated as a genuine All-Marking product achieving the best results in the industry.

Ferro is proud to introduce CerMark **ULTRA**, the only product required to do everything you need in laser bonding.

## Same quality – same high contrasting marks

The newly developed CerMark **ULTRA** Aerosol & Paste continues the tradition set by the Cermark LMM-6000 & LMM-14 delivering the same high contrast, quality laser marks.

## Same durability as LMM-6000 & LMM-14

Resistant to common strong acids, bases, organic solvents and extreme heat or cold. In addition to good salt spray resistance, scratch resistance and QUV resistance.

## Will not stain (tarnish) sensitive metals

Will not stain or tarnish sensitive metals such as brass, copper, sterling silver & others.

## A genuine All in one product

The newly developed CerMark **ULTRA** offers improved performance delivering the highest quality mark in the industry for metals, glass, ceramics and more. No need to have more than one marking material in your shop, the newly developed Black CerMark **ULTRA** will do it all.

## Wider laser setting parameters

The CerMark **ULTRA** increases your processing window allowing for either faster speeds or lower power.

## Same handling qualities as the LMM-6000

Same handling characteristics as LMM-6000, which means, once dry, the **ULTRA** will not rub off on your fingers while handling. This will allow you to coat your parts today, stock the parts and laser mark when needed.

## Fast drying same as the LMM-6000

Formulated with alcohol for faster drying time. Dilution ratios remains the same as LMM-6000 & LMM-14, 1:1 for spraying and 2:1 for brush on applications.

## Improved Aerosol performance

Eliminates the need to clear the spray system by inverting the can and spray after use. A specially designed spray system was introduced in the manufacturing of the new CerMark **ULTRA** Aerosol can allowing for improved usage.

